

Email : sales@engineeringlabchina.com



Tube bundle : Number of tubes: 23 One tube in variable position is heated Heating power: 20W Heat transfer area: 0,001m2

Cylinder with an even temperature at the surface : Heating power: 20W Heat transfer area: 0,0112m2

Plate : Heating power: 40W Heat transfer area: 2x 0,01m2

Cylinder with heating foil to investigate the local heat transfer : Heating power: 40W Heat transfer area: 0,0112m2

Axial fan : Max. Flow rate: 500m3/h Max. Pressure difference: approx. 950Pa Power consumption: 90W

Measuring ranges : Air velocity: 0...10m/s Temperature: 4x 0...325°C Heating power: 0...50W

Required for Operation : 230V, 50Hz, 1 phase 230V, 60Hz, 1 phase; 120V, 60Hz, 1 phase



Engineering Lab China